

## Release Notes for Firmware of H&H ERI Series Electronic Loads

Contact H&H to check possibility of firmware update for your specific device. Provide serial number.

Concerning Components:

AI: Analog Interface Board  
DI: Data Interface Board  
UI: User Interface Board  
GI: GPIB Interface Board

Höcherl & Hackl GmbH  
Industriestr. 13  
94357 Konzell  
GERMANY  
Tel.: 0049 09963/94301-0  
Fax: 0049 09963/94301-84  
[support@hoecherl-hackl.com](mailto:support@hoecherl-hackl.com)  
[www.hoecherl-hackl.com](http://www.hoecherl-hackl.com)

## Firmware Release: AI2.0.3 DI2.0.1 UI2.0.2

### Enhancements / Changed

- Optimized synchronization between voltage protection and ZV functionality.
- Optimized controlling of cooling fan.

### Backwards Compatible

Hardware: Yes

Software: Yes

## Firmware Release: AI2.0.2 DI2.0.1 UI2.0.2

### Enhancements / Changed

- Optimized synchronization of device functions with remote shutdown.
- Optimized re-synchronization with external ADC after firmware update.
- Restricted control of USB logging function to local operation mode.
- Prevented start of USB logging controlled by the discharge function during execution of follow-up time.
- Added status "Fu logging" to the discharge main screen.
- Improved wrapping function in Technical Data dialog.
- Improved comparison of Toggle Settings in Mode dialogs.
- Enhanced Reset, Save and Recall commands.
- Enhanced cooling mode in Master mode.

### Bugfixes / Corrected

- Corrected error in master-slave mode for checking type of slave devices.
- Fixed bug that in some cases unit "mmA" for the setting value was displayed.

### Backwards Compatible

Hardware: Yes

Software: Yes

## Firmware Release: AI2.0.1 DI2.0.0 UI2.0.1

### Enhancements / Changed

- Added continuous execution of the data logging function for the main graph view.
- Added Main Screen and Graph Screen Settings dialogs to the menu content of slave devices.
- Added possibility to enter the relative adjustment points with one decimal place.
- Replaced temperature unit text "deg C" by "°C" in Cooling dialog window.

### Backwards Compatible

Hardware: Yes

Software: Yes

## Firmware Release: AI2.0.1 DI2.0.0 UI2.0.0

### Enhancements / Changed

- Optimized controlling of cooling fan.

### Backwards Compatible

Hardware: No – needs AI board with Rev. 5 or higher and corresponding regulation board  
Software: Yes

## Firmware Release: AI2.0.0 DI2.0.0 UI2.0.0

### **First firmware version for production series B**

### New Features/Added

- Added master-slave functionality.
- Added functionality for internal resistance measurement.
- Added functionality for calculation of calibration parameters.
- Added functionality for requesting slow or fast measurement values.
- Added functionality for getting status of memory positions for settings.
- Added parameters for faster and slow power regulation.
- Added functionality for diagnostic values.
- Added support for software bootloader.
- Added command/query for configuration of CAN termination.
- Added commands/queries for user-specific messages and signal tones.
- Added commands/queries for automated calibration.
- Added query for diagnostic values.
- Added help system for each screen in German and English language.
- Added screenshot functionality.
- Added rectangular functionality with function specific main screen.
- Added configurable Graph main screen.
- Added extended MPPT functionality.
- Added MPPT Graph main screen.
- Added a LIST function specific main screen.
- Added combined Discharge/List functionality.
- Added scaled value input for settings which are smaller than 1.0F (e.g.  $R_{max} = 0.47 \text{ Ohm}$ ), these values are now displayed with unit prefix "m" (e.g. 477 mOhm).
- Added Toggle Setting functionality for simple one-click changes on UI.
- Added displaying of max. resistance value in Technical Data screen.
- Added firmware versions and system unit mode to the exported setting file.
- Added Alarms dialog.
- Added validation of the internal memory positions before loading settings.
- Added possibility to update GPIB firmware during initial operation and in production mode.
- Added shortcut popup window.

### Enhancements / Changed

- Extended measurement data buffer from 8,000 to 40,000.
- Extended number of setting memory positions.
- Extended discharge functionality.

- Extended list functionality.
- Extended trigger functionality.
- Extended error detection.
- Extended query for measurement values.
- Changed parameter list structure.
- Changed resolution of slow ADC from 18 to 23 bits.
- Changed resolution of fast ADC from 12 to 16 bits.
- Changed maximum value for list count (from 4.0E+09 to 999,999).
- Changed maximum value for dwell and ramp time (from 800,000s to 1,000s).
- Changed maximum value for sampling time (from 800,000s to 1,000s).
- Changed reset value for regulation state of voltage protection (from ON to OFF).
- Changed the directory name pattern for USB exports (new ERI\_Sn12345).
- Extended sample time for USB data logging.
- Enhanced indication of RV and OV alarms in order to allow entering the menu during pending RV or OV conditions.

## Bugfixes / Corrected

none

## Backwards Compatible

Hardware: No - firmware only for ERI production series B

Software: No – see changes

## Firmware Release: AI1.0.1 DI1.0.1 UI1.0.0

### Enhancements / Changed

- Changed firmware startup sequence after hardware-specific changes on AI.

## Backwards Compatible

Hardware: Yes

Software: Yes

## Firmware Release: AI1.0.0 DI1.0.1 UI1.0.0

### Enhancements / Changed

- Activated internal pull-up resistors for input signals of serial interface to optional GPIB components on DI

## Backwards Compatible

Hardware: Yes

Software: Yes

## Firmware Release: AI1.0.0 DI1.0.0 UI1.0.0

Initial Release